










Wip voor wippenet 2-voudig voor tastsensor 4.95



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 aluminium zuiver wit glanzend (gelakt)	8332 903	1	57,13	06	4010337098713
 aluminium zuiver wit mat (gelakt)	8332 927	1	57,13	06	4010337098737
 aluminium antraciet (gelakt)	8332 928	1	57,13	06	4010337098676
 aluminium (geanodiseerd)	8332 17	1	45,10	06	4010337096979
 aluminium zwart mat (gelakt)	8332 905	1	57,13	06	4010337098690
 aluminium grijs mat (gelakt)	8332 915	1	57,13	06	4010337098652
 aluminium zwart (geanodiseerd)	8332 126	1	45,10	06	4010337096993
 Brons (PVD)	8332 38	1	96,21	06	4010337098751
 glas wit	8332 12	1	45,10	06	4010337097792

	glas zwart	8332 05	1	45,10	06	4010337098027
	edelstaal	8332 219	1	78,18	06	4010337097334