












Wip voor wippenet 4-voudig voor tastsensor 4.95



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 aluminium zuiver wit glanzend (gelakt)	8334 903	1	45,10	06	4010337098720
 aluminium zuiver wit mat (gelakt)	8334 927	1	45,10	06	4010337098744
 aluminium antraciet (gelakt)	8334 928	1	45,10	06	4010337098683
 aluminium (geanodiseerd)	8334 17	1	33,08	06	4010337096986
 aluminium zwart mat (gelakt)	8334 905	1	45,10	06	4010337098706
 aluminium grijs mat (gelakt)	8334 915	1	45,10	06	4010337098669
 aluminium zwart (geanodiseerd)	8334 126	1	33,08	06	4010337097228
 Brons (PVD)	8334 38	1	78,18	06	4010337098775
 glas wit	8334 12	1	33,08	06	4010337098010

 glas zwart	8334 05	1	33,08	06	4010337098034
<hr/>					
 edelstaal	8334 219	1	60,13	06	4010337097785
<hr/>					