













Wip voor wippenet 4-voudig voor tastsensor 4.95



| Spezifikation | Bestell-Nr. | VE | EUR/Stück o. MWSt. | PS | EAN |
|--|-------------|----|--------------------|----|---------------|
|  aluminium zuiver wit glanzend (gelakt) | 8334 903 | 1 | 45,10 | 06 | 4010337098720 |
|  aluminium zuiver wit mat (gelakt) | 8334 927 | 1 | 45,10 | 06 | 4010337098744 |
|  aluminium antraciet (gelakt) | 8334 928 | 1 | 45,10 | 06 | 4010337098683 |
|  aluminium (geanodiseerd) | 8334 17 | 1 | 33,08 | 06 | 4010337096986 |
|  aluminium zwart mat (gelakt) | 8334 905 | 1 | 45,10 | 06 | 4010337098706 |
|  aluminium grijs mat (gelakt) | 8334 915 | 1 | 45,10 | 06 | 4010337098669 |
|  aluminium zwart (geanodiseerd) | 8334 126 | 1 | 33,08 | 06 | 4010337097228 |
|  Brons (PVD) | 8334 38 | 1 | 78,18 | 06 | 4010337098775 |
|  glas wit | 8334 12 | 1 | 33,08 | 06 | 4010337098010 |

| | | | | | |
|--|----------|---|-------|----|---------------|
|  glas zwart | 8334 05 | 1 | 33,08 | 06 | 4010337098034 |
| <hr/> | | | | | |
|  edelstaal | 8334 219 | 1 | 60,13 | 06 | 4010337097785 |
| <hr/> | | | | | |