







Afdekraam Gira F300 grijs mat (gelakt)



| Specificatie | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN |
|---|----------|------|--------------------|----|---------------|
|  1-voudig | 0211 86 | 1/10 | 15,72 | 11 | 4010337113492 |
|  2-voudig | 0212 86 | 1/10 | 23,87 | 11 | 4010337113522 |
|  2-voudig zonder middenstijl | 1002 86 | 1/10 | 23,87 | 11 | 4010337131915 |
|  3-voudig | 0213 86 | 1/5 | 39,26 | 11 | 4010337113577 |
|  4-voudig | 0214 86 | 1/5 | 63,77 | 11 | 4010337113621 |
|  5-voudig | 0215 86 | 1/5 | 97,03 | 11 | 4010337131908 |

Kenmerken

- In de kleurvariant puur wit glanzend: bestaat voor 85 % uit bio-circulair kunststof.

Technische gegevens

| | |
|---------------------|---------------------------|
| Afdekraam 1-v: | B 80,8 x H 80,8 x T 11,4 |
| Afdekraam 2-v: | B 80,8 x H 151,9 x T 11,4 |
| Afdekraam 2-v z/ms: | B 80,8 x H 151,9 x T 11,4 |

| | |
|--------------------------------------|---------------------------|
| Afdekraam 3-v: | B 80,8 x H 223,4 x T 11,4 |
| Afdekraam 4-v: | B 80,8 x H 297,7 x T 11,4 |
| Afdekraam 5f: | B 80,8 x H 366,0 x T 11,4 |
| Hoekradius: | R 0,5 |
| Biocirculair kunststof | |
| - Kleurvariant: zuiver wit glanzend: | min. 50% |
