







## Afdekraam Gira F100 zuiver wit glanzend



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 1-voudig	0211 112	1/10	9,70	01	4010337043973
 2-voudig	0212 112	1/10	13,32	01	4010337044017
 2-voudig zonder middenstijl	1002 112	1/10	13,32	01	4010337047094
 3-voudig	0213 112	1/5	24,30	01	4010337044031
 4-voudig	0214 112	1/5	39,25	01	4010337044055
 5-voudig	0215 112	1/5	59,89	01	4010337044079

### Kenmerken

- Breukvast.
- In de kleurvariant puur wit glanzend: bestaat voor 85 % uit bio-circulair kunststof.

### Technische gegevens

Afdekraam 1-v:	B 83,3 x H 83,3 x T 10,6
Afdekraam 2-v:	B 83,3 x H 154,4 x T 10,6
Afdekraam 2-v z/ms:	B 83,3 x H 154,4 x T 10,6

Afdekraam 3-v: B 83,3 x H 225,9 x T 10,6

Afdekraam 4-v: B 83,3 x H 297,2 x T 10,6

Afdekraam 5f: B 83,3 x H 368,5 x T 10,6

Hoekradius: R 3

Biocirculair kunststof

- Kleurvariant: zuiver wit glanzend: min. 50%

---

## Aanwijzingen

- In combinatie met afdichtflens ook geschikt voor montage spatwaterdicht inbouw IP44.

---