







## Afdekraam Gira F100 antraciet (gelakt)



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 1-voudig	0211 173	1/10	15,72	11	4010337135951
 2-voudig	0212 173	1/10	23,87	11	4010337133568
 2-voudig zonder middenstijl	1002 173	1/10	23,87	11	4010337133605
 3-voudig	0213 173	1/5	39,26	11	4010337133575
 4-voudig	0214 173	1/5	63,77	11	4010337133582
 5-voudig	0215 173	1/5	97,03	11	4010337133599

### Kenmerken

- In de kleurvariant puur wit glanzend: bestaat voor 85 % uit bio-circulair kunststof.

### Technische gegevens

Afdekraam 1-v:	B 83,3 x H 83,3 x T 10,6
Afdekraam 2-v:	B 83,3 x H 154,4 x T 10,6
Afdekraam 2-v z/ms:	B 83,3 x H 154,4 x T 10,6

Afdekraam 3-v: B 83,3 x H 225,9 x T 10,6

Afdekraam 4-v: B 83,3 x H 297,2 x T 10,6

Afdekraam 5f: B 83,3 x H 368,5 x T 10,6

Hoekradius: R 3

Biocirculair kunststof  
- Kleurvariant: zuiver wit glanzend: min. 50%

---