







## Afdekraam Gira E2



| Specificatie  | Art. nr. | VE   | EUR/stuk excl. BTW | PS | EAN           |
|---|----------|------|--------------------|----|---------------|
|  1-voudig                      | 0211 33  | 1/10 | 24,79              | 11 | 4010337019794 |
|  2-voudig                    | 0212 33  | 1/10 | 38,41              | 11 | 4010337019800 |
|  2-voudig zonder middenstijl | 1002 33  | 1/10 | 38,41              | 11 | 4010337019848 |
|  3-voudig                    | 0213 33  | 1/5  | 70,61              | 11 | 4010337019817 |
|  4-voudig                    | 0214 33  | 1/5  | 109,57             | 11 | 4010337019824 |
|  5-voudig                    | 0215 33  | 1/5  | 166,88             | 11 | 4010337019831 |

### Aanwijzingen

- Ook geschikt voor wandgootinstallatie.
- Afdekraam (1- tot 5-voudig) in combinatie met afdichtset ook geschikt voor installatie spatwaterdicht inbouw IP44.