

Dubbele wandcontactdoos met randaarde 16 A 250 V~ met verhoogde aanraakbeveiliging (Safety Plus) en vaste afdekplaat voor inbouwapparaatdoos 1-voudig Steekklemmen



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	0783 01	1/10	28,57	01	4010337783015
 zuiver wit glanzend	0783 03	1/10	28,57	01	4010337783039
 zuiver wit mat	0783 27	1	28,57	01	4010337783275
 antraciet	0783 28	1	31,95	11	4010337783282
 kleur aluminium	0783 26	1/10	37,09	11	4010337783268
 zwart mat	0783 005	1	37,09	11	4010337037507
 grijs mat	0783 015	1/10	37,09	11	4010337081876

Technische gegevens

Inbouwdiepte: 25 mm

Aansluitingdoorsnede
- voor geleiders van: 1,5 mm² tot 2,5 mm²

Omgevingstemperatuur
- verhoogde aanraakbeveiliging: 0 °C tot +45 °C

Aanwijzingen

- Passend in alle gangbare apparaatdozen.
 - Verhoogde aanraakbeveiliging (Safety Plus) conform DIN VDE 0620-1.
-