


## Wippenet 2-voudig (1+1) System 55



| Specificatie                                                                                                     | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN           |
|------------------------------------------------------------------------------------------------------------------|----------|----|--------------------|----|---------------|
|  crème wit glanzend (gelakt)    | 2182 01  | 1  | 23,76              | 06 | 4010337012092 |
|  zuiver wit glanzend (gelakt) | 2182 03  | 1  | 23,76              | 06 | 4010337012115 |
|  zuiver wit mat (gelakt)      | 2182 27  | 1  | 23,76              | 06 | 4010337013372 |
|  antraciet (gelakt)           | 2182 28  | 1  | 27,23              | 06 | 4010337012139 |
|  kleur aluminium (gelakt)     | 2182 26  | 1  | 31,14              | 06 | 4010337012122 |
|  zwart mat (gelakt)           | 2182 005 | 1  | 31,14              | 06 | 4010337038320 |
|  grijs mat (gelakt)           | 2182 015 | 1  | 31,14              | 06 | 4010337083160 |
|  edelstaal                    | 2132 601 | 1  | 21,83              | 06 | 4010337020059 |

## Aanwijzingen

- Beschrijfbare wippensets en wippensets zonder tekstkader zijn van metaal, dit kan bij draadloze toepassingen het bereik beperken.
-