








Aardlekschakelaar 30 mA



| Specificatie | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN |
|---|----------|----|--------------------|----|---------------|
|  crème wit glanzend | 2664 01 | 1 | 167,90 | 03 | 4010337011897 |
|  zuiver wit glanzend | 2664 03 | 1 | 167,90 | 03 | 4010337011903 |
|  zuiver wit mat | 2664 27 | 1 | 167,90 | 03 | 4010337011910 |
|  antraciet | 2664 28 | 1 | 168,58 | 03 | 4010337011927 |
|  kleur aluminium | 2664 26 | 1 | 170,28 | 03 | 4010337011934 |
|  zwart mat | 2664 005 | 1 | 170,28 | 03 | 4010337037064 |
|  grijs mat | 2664 015 | 1 | 170,28 | 03 | 4010337085232 |

Kenmerken

- De aardlekschakelaar is een vaste beveiligingsinrichting met spanningsonafhankelijke lekstroomactivering conform VDE 0664.
- Werkingsprincipe komt overeen met dat van een aardlekschakelaar.

Technische gegevens

| | |
|---|---|
| Nominale spanning: | AC 230 V, 50/60 Hz |
| Nominale stroom: | 16 A |
| Nominale lekstroom: | 30 mA |
| Inbouwdiepte: | 32 mm |
| Aansluitingdoorsnede - voor geleiders van: | 1,5 mm ² tot 2,5 mm ² |
| Omgevingstemperatuur: | -25 °C tot +40 °C |

Aanwijzingen

- Toepassingsgebieden: Wandgoten, voor wandcontactdozen of in Gira energiezuilen.
 - Montage in een diepe apparaatdoos.
-