








Dubbele wandcontactdoos met randaarde 16 A 250 V~ met verhoogde aanraakbeveiliging (Safety Plus) voor inbouwapparaatdoos 1-voudig



| Specificatie | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN |
|---|----------|------|--------------------|----|---------------|
|  crème wit glanzend | 2731 01 | 1/10 | 27,86 | 01 | 4010337881100 |
|  zuiver wit glanzend | 2731 03 | 1/10 | 27,86 | 01 | 4010337881117 |
|  zuiver wit mat | 2731 27 | 1/10 | 27,86 | 01 | 4010337881124 |
|  antraciet | 2731 28 | 1/10 | 31,22 | 11 | 4010337000778 |
|  kleur aluminium | 2731 26 | 1/10 | 36,40 | 11 | 4010337000761 |
|  zwart mat | 2731 005 | 1/10 | 36,40 | 11 | 4010337037538 |
|  grijs mat | 2731 015 | 1/10 | 36,40 | 11 | 4010337085256 |

Technische gegevens

| | |
|---|---|
| Inbouwdiepte: | 25 mm |
| Aansluitingdoorsnede - voor geleiders van: | 1,5 mm ² tot 2,5 mm ² |
| Omgevingstemperatuur - verhoogde aanraakbeveiliging: | 0 °C tot +45 °C |

Opbouwhoogte: 17,5 mm

Aanwijzingen

- Passend in alle gangbare apparaatdozen.
 - Verhoogde aanraakbeveiliging (Safety Plus) conform DIN VDE 0620-1.
-