








Dubbele wandcontactdoos met randaarde 16 A 250 V~ met verhoogde aanraakbeveiliging (Safety Plus) voor inbouwapparaatdoos 1,5-voudig



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	2735 01	1/10	27,86	01	4010337000822
 zuiver wit glanzend	2735 03	1/10	27,86	01	4010337771371
 zuiver wit mat	2735 27	1/10	27,86	01	4010337771555
 antraciet	2735 28	1/10	31,22	11	4010337771364
 kleur aluminium	2735 26	1/10	36,40	11	4010337000785
 zwart mat	2735 005	1/10	36,40	11	4010337037521
 grijs mat	2735 015	1/10	36,40	11	4010337085294

Technische gegevens

Inbouwdiepte:	25 mm
Aansluitingdoorsnede - voor geleiders van:	1,5 mm ² tot 2,5 mm ²
Opbouwhoogte:	6 mm

Aanwijzingen

- Geschikt voor compact-inbouwdozen Attema UK 40 en type H 140 van ABB/HAF.
 - Verhoogde aanraakbeveiliging (Safety Plus) conform DIN VDE 0620-1.
-