








## Wipschakelaar British Standard (BS EN 60669-1) 3-voudig met wippen Schakelaar



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	2830 01	1/10	25,77	29	4010337830016
 zuiver wit glanzend	2830 03	1/10	25,77	29	4010337830030
 antraciet	2830 28	1/10	28,38	29	4010337830283
 kleur aluminium	2830 26	1/10	32,27	29	4010337830269
 zwart mat	2830 005	1/10	32,27	29	4010337038580
 grijs mat	2830 015	-	-	-	4010337087113
 edelstaal (gelakt)	2830 600	1/10	35,89	29	4010337022022

### Technische gegevens

Inbouwdiepte:	25 mm
Aansluitingdoorsnede - voor geleiders tot:	2,5 mm <sup>2</sup>
Nominaal vermogen:	100 W ledbelasting (IEC 60669)