

Universele uit-wisselschakelaar



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	2832 01	1/10	36,52	29	4010337832010
 zuiver wit glanzend	2832 03	1/10	36,52	29	4010337832034
 antraciet	2832 28	1/10	39,25	29	4010337832287
 kleur aluminium	2832 26	1/10	43,42	29	4010337832263
 zwart mat	2832 005	1/10	54,19	11	4010337038528
 grijs mat	2832 015	1/10	54,19	11	4010337087120
 edelstaal (gelakt)	2832 600	1/10	47,29	29	4010337022053

Technische gegevens

Inbouwdiepte: 25 mm

Aansluitingdoorsnede
- voor geleiders tot: 2,5 mm²

Aanwijzingen

- Uitsluitend voor schroefbevestiging.
