








## Wipchakelaar British Standard (BS EN 60669-1) 20 AX 250 V~ met wip Schakelaar 2-polig



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	2836 01	1/10	38,99	29	4010337078944
 zuiver wit glanzend	2836 03	1/10	38,99	29	4010337078951
 antraciet	2836 28	1/10	39,71	29	4010337078975
 kleur aluminium	2836 26	1/10	42,87	29	4010337078968
 zwart mat	2836 005	1/10	42,87	29	4010337038566
 grijs mat	2836 015	1/10	42,87	29	4010337087144
 edelstaal	2836 600	1/10	49,81	29	4010337021933

### Technische gegevens

Inbouwdiepte:	24 mm
Aansluitingdoorsnede - voor geleiders tot:	2 x 4 mm <sup>2</sup> of 1 x 6 mm <sup>2</sup>

## Aanwijzingen

- Uitsluitend voor schroefbevestiging.
  - BS EN 60669-1.
-