


## Wipschakelaar 10 AX 250 V~ met wip 2-voudig voor weergave hotelkamerstatus



| Specificatie                                                                                                 | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN           |
|--------------------------------------------------------------------------------------------------------------|----------|----|--------------------|----|---------------|
|  crème wit glanzend         | 3104 01  | 1  | 51,43              | 01 | 4010337042495 |
|  zuiver wit glanzend      | 3104 03  | 1  | 51,43              | 01 | 4010337042501 |
|  zuiver wit mat           | 3104 27  | 1  | 51,43              | 01 | 4010337042525 |
|  antraciet                | 3104 28  | 1  | 52,08              | 11 | 4010337042532 |
|  kleur aluminium (gelakt) | 3104 26  | 1  | 56,32              | 11 | 4010337042518 |
|  zwart mat (gelakt)       | 3104 005 | 1  | 56,32              | 11 | 4010337069812 |

### Kenmerken

- Schakelaar voor weergave hotelkamerstatus "Do not disturb" en "Make up room".
- Met vergrendeling tegen dubbelzijdig inschakelen.
- Elektrisch en mechanisch vergrendeld.

### Technische gegevens

Inbouwdiepte: 32 mm

Aansluitingdoorsnede  
- voor massieve en soepele geleiders tot: 2,5 mm²

Nominaal vermogen  
- LEDi/ CFLi:

100 W

---