


## Rechtstaande wip 2-voudig System 70



| Specificatie                                                                                                | Art. nr. | VE   | EUR/stuk excl. BTW | PS | EAN           |
|-------------------------------------------------------------------------------------------------------------|----------|------|--------------------|----|---------------|
|  zuiver wit glanzend       | 3495 70  | 1/10 | 12,09              | 01 | 4010337118848 |
|  zuiver wit mat (gelakt) | 3495 72  | 1/10 | 17,11              | 11 | 4010337118855 |
|  antraciet (gelakt)      | 3495 73  | 1/10 | 17,11              | 11 | 4010337118862 |
|  zwart mat (gelakt)      | 3495 74  | 1/10 | 17,11              | 11 | 4010337118886 |
|  grijs mat (gelakt)      | 3495 76  | 1/10 | 17,11              | 11 | 4010337118879 |