


## Plug-in-enhet for datahette for Modular Jack AMP



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Dobbel	0039 00	1/5/25		4010337039006

### Merknader

- Passer til: AMP 6-polet 1116603-1 toolless kat.3AMP 8-polet 1116515-1 kat.5e skjernetAMP 8-polet 1116604-1 toolless kat.5e uskjernetAMP 8-polet 1339015-1 toolless kat.5e skjernetAMP 8-polet 1375055-1 SL kat.6 uskjernetAMP 8-polet 1375188-1 SL kat.6 skjernetKannegieter BICC Brand Rex Snap-In-Jacks RJ45Krone Inline RJ45 skjernet/uskjernetAMP SL Series RJ45 Jack kat.5EAMP TWIST-7AS SL Jack 8-polet 1711441-1 skjernet kat.7AMP TWIST-7AS SL Jack 8-polet 1711437-1 skjernet kat.7AMP TWIST-6S SL Jack 8-polet 1711160-1 skjernet kat.6AMP TWIST-6S SL Jack 8-polet 1711342-1 skjernet kat.6AMP TWIST-6AS SL Jack 8-polet 1711592-1 skjernet kat.6AMP TWIST-6AS SL Jack 8-polet 1711716-1 skjernet kat.6AMP LC LWL Duplex-adapterAMP MT RJ LWL Duplex.
- Det andre hullet kan stenges.