



Kortslagstrykknapp 0,5 A 42 V~ med vippe Lukkekontakt 1-polet



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|---|-----------------|-----|----|---------------|
|  kremhvit glans | 0138 01 | - | - | 4010337138013 |
|  renhvit glans | 0138 03 | 1/5 | - | 4010337138037 |
|  renhvit silkematt | 0138 27 | - | - | 4010337138273 |
|  antrasitt | 0138 28 | - | - | 4010337138280 |
|  aluminiumsfarget | 0138 26 | - | - | 4010337138266 |
|  svart matt | 0138 005 | - | - | 4010337037262 |

Egenskaper

- Med skruklemmer.

Tekniske data

Monteringsdybde: 11 mm

Merknader

- For klem- og dyvelfeste.
