








Dekkramme Gira Standard 55 renhvit glans



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 03 1420752	1/10/100		4010337211037
 1,5-dobbel	1001 03 1522581	1/10		4010337881308
 Dobbel	0212 03 1420753	1/10/100		4010337212034
 dobbel, uten mellomstykke	1002 03 1420751	1/10		4010337001607
 3-dobbel	0213 03 1420754	1/10/100		4010337213031
 4-dobbel	0214 03 1420755	1/5		4010337214038
 5-dobbel	0215 03 1420756	1/5		4010337215035

Egenskaper

- Plast: halogenfri, slag- og bruddsikker termoplast, eller heter det da polykarbonat.

Merknader

- Også egnet for kanalinstallasjoner.
 - Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.
-