

## Dekkramme Gira Standard 55 renhvit silkematt



| Spesifikasjon                                                                                                 | Bestillings nr.    | PE       | PS | EAN           |
|---------------------------------------------------------------------------------------------------------------|--------------------|----------|----|---------------|
|  Enkel                       | 0211 04<br>1420501 | 1/10/100 |    | 4010337211044 |
|  1,5-dobbel                | 1001 04            | 1/10     |    | 4010337881315 |
|  Dobbel                    | 0212 04<br>1420005 | 1/10/100 |    | 4010337212041 |
|  dobbel, uten mellomstykke | 1002 04            | 1/10     |    | 4010337002048 |
|  3-dobbel                  | 0213 04<br>1420006 | 1/10/100 |    | 4010337213048 |
|  4-dobbel                  | 0214 04<br>1420015 | 1/5      |    | 4010337214045 |
|  5-dobbel                  | 0215 04<br>1420016 | 1/5      |    | 4010337215042 |

### Egenskaper

- Plast: halogenfri, slag- og bruddsikker termoplast, eller heter det da polykarbonat.

## Merknader

- Også egnet for kanalinstallasjoner.
  - Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.
-