








Dekkramme Gira E2 svart matt



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 09 1499901	1/10		4010337036739
 1,5-dobbel	1001 09	1/10		4010337072775
 Dobbel	0212 09 1499902	1/10		4010337036760
 dobbel, uten mellomstykke	1002 09 1499903	1/10		4010337036784
 3-dobbel	0213 09 1499904	1/5		4010337036821
 4-dobbel	0214 09 1499905	1/5		4010337036869
 5-dobbel	0215 09 1499906	1/5		4010337036906

Egenskaper

- Plast: halogenfri, slag- og bruddsikker termoplast, eller heter det da polykarbonat.

Merknader

- Også egnet for kanalinstallasjoner.
 - Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.
-