








## Dekkramme Gira Esprit aluminium brun (eloksert)



| Spesifikasjon   | Bestillings nr.     | PE | PS | EAN           |
|---|---------------------|----|----|---------------|
|  Enkel                       | 0211 127<br>1478873 | 1  |    | 4010337109075 |
|  1,5-dobbel                | 1001 127            | 1  |    | 4010337881537 |
|  Dobbel                    | 0212 127<br>1478874 | 1  |    | 4010337109082 |
|  dobbel, uten mellomstykke | 1002 127            | 1  |    | 4010337109136 |
|  3-dobbel                  | 0213 127<br>1478875 | 1  |    | 4010337109099 |
|  4-dobbel                  | 0214 127<br>1478876 | 1  |    | 4010337109112 |

### Egenskaper

- Elokstert aluminium E 1. Fargeavvik mulig.