








Dekkramme Gira E2 antrasitt



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 23 1420519	1/10/100		4010337211235
 1,5-dobbel	1001 23 1522591	1/10		4010337881339
 Dobbel	0212 23 1420560	1/10/100		4010337212232
 dobbel, uten mellomstykke	1002 23 1420205	1/10		4010337002239
 3-dobbel	0213 23 1420597	1/5		4010337213239
 4-dobbel	0214 23 1420628	1/5		4010337214236
 5-dobbel	0215 23 1420660	1/5		4010337215233

Egenskaper

- Plast: halogenfri, slag- og bruddsikker termoplast, eller heter det da polykarbonat.

Merknader

- Også egnet for kanalinstallasjoner.
 - Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.
-