

Dekkramme Gira E2 aluminiumsfarget (lakkert)



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 25 1420521	1/10/100		4010337211259
 1,5-dobbel	1001 25 1522592	1/10		4010337881346
 Dobbel	0212 25 1420562	1/10		4010337212256
 dobbel, uten mellomstykke	1002 25 1420207	1/10		4010337002253
 3-dobbel	0213 25 1420599	1/5		4010337213253
 4-dobbel	0214 25 1420630	1/5		4010337214250
 5-dobbel	0215 25 1420662	1/5		4010337215257

Egenskaper

- Plast: halogenfri, slag- og bruddsikker termoplast, eller heter det da polykarbonat.

Merknader

- Også egnet for kanalinstallasjoner.
 - Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.
-