

Dekkramme Gira E2 renhvit glans



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 29 1420758	1/10/100		4010337211297
 1,5-dobbel	1001 29 1522593	1/10		4010337881353
 Dobbel	0212 29 1420759	1/10/100		4010337212294
 dobbel, uten mellomstykke	1002 29 1420757	1/10		4010337001553
 3-dobbel	0213 29 1420760	1/5		4010337213291
 4-dobbel	0214 29 1420761	1/5		4010337214298
 5-dobbel	0215 29 1420762	1/5		4010337215295

Egenskaper

- Plast: halogenfri, slag- og bruddsikker termoplast, eller heter det da polykarbonat.

Merknader

- Også egnet for kanalinstallasjoner.
 - Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.
-