






## Dekkramme Gira E2



| Spesifikasjon   | Bestillings nr.    | PE   | PS | EAN           |
|---|--------------------|------|----|---------------|
|  Enkel                       | 0211 33<br>1479215 | 1/10 |    | 4010337019794 |
|  Dobbel                    | 0212 33<br>1479206 | 1/10 |    | 4010337019800 |
|  dobbel, uten mellomstykke | 1002 33<br>1479230 | 1/10 |    | 4010337019848 |
|  3-dobbel                  | 0213 33<br>1479218 | 1/5  |    | 4010337019817 |
|  4-dobbel                  | 0214 33<br>1479219 | 1/5  |    | 4010337019824 |
|  5-dobbel                  | 0215 33<br>1479228 | 1/5  |    | 4010337019831 |

### Merknader

- Også egnet for kanalinstallasjoner.
- Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.