

Dekkramme Gira F200 renhvit silkematt (lakkert)



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 72	1/10		4010337113188
 Dobbel	0212 72	1/10		4010337113232
 dobbel, uten mellomstykke	1002 72	1/10		4010337113447
 3-dobbel	0213 72	1/5		4010337113287
 4-dobbel	0214 72	1/5		4010337113348
 5-dobbel	0215 72	1/5		4010337113393

Tekniske data

Dekkramme enk.:	B 90,0 x H 90,0 x T 11,4
Dekkramme dob.:	B 90,0 x H 161,1 x T 11,4
Dekkramme dob. u/MS:	B 90,0 x H 161,1 x T 11,4
Dekkramme 3-d:	B 90,0 x H 232,6 x T 11,4
Dekkramme 4-d:	B 90,0 x H 303,9 x T 11,4
Dekkramme 5-d:	B 90,0 x H 375,2 x T 11,4
Hjørneradius:	R 0,3

