





Dekkramme Gira F200 for flat innbygging renhvit glans



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 705	1/10/100		4010337108900
 Dobbel	0212 705	1/10		4010337108986
 3-dobbel	0213 705	1/5		4010337109310
 4-dobbel	0214 705	1/5		4010337109365

Egenskaper

- I fargen ren hvit, blank: består av 85 % resirkulert plast.

Tekniske data

Dekkramme enk.:	B 90,0 x H 90,0 x T 3,4
Dekkramme dob.:	B 90,0 x H 161,1 x T 3,4
Dekkramme 3-d:	B 90,0 x H 232,6 x T 3,4
Dekkramme 4-d:	B 90,0 x H 303,9 x T 3,4
Hjørneradius:	R 0,3
Biocirkulær plast - Farge: renhvit glans:	min. 50 %