







Dekkramme Gira F200 grå matt (lakkert)



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|---------------------------------------------------------------------------------------------------------------|-----------------|------|----|---------------|
|  Enkel | 0211 76 | 1/10 | | 4010337113164 |
|  Dobbel | 0212 76 | 1/10 | | 4010337113218 |
|  dobbel, uten mellomstykke | 1002 76 | 1/10 | | 4010337113423 |
|  3-dobbel | 0213 76 | 1/5 | | 4010337113263 |
|  4-dobbel | 0214 76 | 1/5 | | 4010337113324 |
|  5-dobbel | 0215 76 | 1/5 | | 4010337113379 |

Egenskaper

- I fargen ren hvit, blank: består av 85 % resirkulert plast.

Tekniske data

| | |
|----------------------|---------------------------|
| Dekkramme enk.: | B 90,0 x H 90,0 x T 11,4 |
| Dekkramme dob.: | B 90,0 x H 161,1 x T 11,4 |
| Dekkramme dob. u/MS: | B 90,0 x H 161,1 x T 11,4 |

| | |
|----------------------------------------------|---------------------------|
| Dekkramme 3-d: | B 90,0 x H 232,6 x T 11,4 |
| Dekkramme 4-d: | B 90,0 x H 303,9 x T 11,4 |
| Dekkramme 5-d: | B 90,0 x H 375,2 x T 11,4 |
| Hjørneradius: | R 0,3 |
| Biocirkulær plast - Farge: renhvit glans: | min. 50 % |
