

Dekkramme Gira F300 renhvit glans



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 80	1/10		4010337113478
 Dobbel	0212 80	1/10		4010337113539
 dobbel, uten mellomstykke	1002 80	1/10		4010337131830
 3-dobbel	0213 80	1/5		4010337113584
 4-dobbel	0214 80	1/5		4010337113638
 5-dobbel	0215 80	1/5		4010337131823

Tekniske data

Dekkramme enk.:	B 80,8 x H 80,8 x T 11,4
Dekkramme dob.:	B 80,8 x H 151,9 x T 11,4
Dekkramme dob. u/MS:	B 80,8 x H 151,9 x T 11,4
Dekkramme 3-d:	B 80,8 x H 223,4 x T 11,4
Dekkramme 4-d:	B 80,8 x H 297,7 x T 11,4
Dekkramme 5-d:	B 80,8 x H 366,0 x T 11,4
Hjørneradius:	R 0,5

