






Dekkramme Gira E2



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 33 1479215	1/10		4010337019794
 Dobbel	0212 33 1479206	1/10		4010337019800
 dobbel, uten mellomstykke	1002 33 1479230	1/10		4010337019848
 3-dobbel	0213 33 1479218	1/5		4010337019817
 4-dobbel	0214 33 1479219	1/5		4010337019824
 5-dobbel	0215 33 1479228	1/5		4010337019831

Merknader

- Også egnet for kanalinstallasjoner.
- Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.