

Dekkramme Gira F200 renhvit glans



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 70	1/10		4010337113171
 Dobbel	0212 70	1/10		4010337113225
 dobbel, uten mellomstykke	1002 70	1/10		4010337113430
 3-dobbel	0213 70	1/5		4010337113270
 4-dobbel	0214 70	1/5		4010337113331
 5-dobbel	0215 70	1/5		4010337113386

Tekniske data

Dekkramme enk.:	B 90,0 x H 90,0 x T 11,4
Dekkramme dob.:	B 90,0 x H 161,1 x T 11,4
Dekkramme dob. u/MS:	B 90,0 x H 161,1 x T 11,4
Dekkramme 3-d:	B 90,0 x H 232,6 x T 11,4
Dekkramme 4-d:	B 90,0 x H 303,9 x T 11,4
Dekkramme 5-d:	B 90,0 x H 375,2 x T 11,4
Hjørneradius:	R 0,3

Illustrasjonene kan avvike fra originalen.

Biocirkulær plast

- Farge: renhvit glans:

min. 50 %