





## Dekkramme Gira F200 for flat innbygging antrasitt (lakkert)



| Spesifikasjon  | Bestillings nr. | PE       | PS | EAN           |
|--|-----------------|----------|----|---------------|
|  Enkel      | 0211 735        | 1/10/100 |    | 4010337108887 |
|  Dobbel   | 0212 735        | 1/10     |    | 4010337108962 |
|  3-dobbel | 0213 735        | 1/5      |    | 4010337109297 |
|  4-dobbel | 0214 735        | 1/5      |    | 4010337109341 |

### Egenskaper

- I fargen ren hvit, blank: består av 85 % resirkulert plast.

### Tekniske data

|  |                          |
|--|--------------------------|
| Dekkramme enk.:                              | B 90,0 x H 90,0 x T 3,4  |
| Dekkramme dob.:                              | B 90,0 x H 161,1 x T 3,4 |
| Dekkramme 3-d:                               | B 90,0 x H 232,6 x T 3,4 |
| Dekkramme 4-d:                               | B 90,0 x H 303,9 x T 3,4 |
| Hjørneradius:                                | R 0,3                    |
| Biocirkulær plast<br>- Farge: renhvit glans: | min. 50 %                |