

Dekkramme Gira F300 renhvit silkematt (lakkert)



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 82	1/10		4010337113485
 Dobbel	0212 82	1/10		4010337113546
 dobbel, uten mellomstykke	1002 82	1/10		4010337131854
 3-dobbel	0213 82	1/5		4010337113591
 4-dobbel	0214 82	1/5		4010337113645
 5-dobbel	0215 82	1/5		4010337131847

Egenskaper

- I fargen ren hvit, blank: består av 85 % resirkulert plast.

Tekniske data

Dekkramme enk.:	B 80,8 x H 80,8 x T 11,4
Dekkramme dob.:	B 80,8 x H 151,9 x T 11,4
Dekkramme dob. u/MS:	B 80,8 x H 151,9 x T 11,4

Illustrasjonene kan avvike fra originalen.

Dekkramme 3-d: B 80,8 x H 223,4 x T 11,4

Dekkramme 4-d: B 80,8 x H 297,7 x T 11,4

Dekkramme 5-d: B 80,8 x H 366,0 x T 11,4

Hjørneradius: R 0,5

Biocirkulær plast
- Farge: renhvit glans: min. 50 %