








Dekkramme Gira Standard 55 renhvit silkematt



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 04 1420501	1/10/100		4010337211044
 1,5-dobbel	1001 04	1/10		4010337881315
 Dobbel	0212 04 1420005	1/10/100		4010337212041
 dobbel, uten mellomstykke	1002 04	1/10		4010337002048
 3-dobbel	0213 04 1420006	1/10/100		4010337213048
 4-dobbel	0214 04 1420015	1/5		4010337214045
 5-dobbel	0215 04 1420016	1/5		4010337215042

Egenskaper

- Plast: halogenfri, slag- og bruddsikker termoplast, eller heter det da polykarbonat.

Merknader

- Også egnet for kanalinstallasjoner.
 - Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.
-