

Dekkramme Gira F100 svart matt (lakkert)



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 174	1/10		4010337135968
 Dobbel	0212 174	1/10		4010337133612
 dobbel, uten mellomstykke	1002 174	1/10		4010337133650
 3-dobbel	0213 174	1/5		4010337133629
 4-dobbel	0214 174	1/5		4010337133636
 5-dobbel	0215 174	1/5		4010337135845

Tekniske data

Dekkramme enk.:	B 83,3 x H 83,3 x T 10,6
Dekkramme dob.:	B 83,3 x H 154,4 x T 10,6
Dekkramme dob. u/MS:	B 83,3 x H 154,4 x T 10,6
Dekkramme 3-d:	B 83,3 x H 225,9 x T 10,6
Dekkramme 4-d:	B 83,3 x H 297,2 x T 10,6
Dekkramme 5-d:	B 83,3 x H 368,5 x T 10,6
Hjørneradius:	R 3

