





Dekkramme Gira F200 for flat innbygging renhvit silkematt (lakkert)



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|--|-----------------|----------|----|---------------|
|  Enkel | 0211 725 | 1/10/100 | | 4010337108948 |
|  Dobbel | 0212 725 | 1/10 | | 4010337108993 |
|  3-dobbel | 0213 725 | 1/5 | | 4010337109327 |
|  4-dobbel | 0214 725 | 1/5 | | 4010337109372 |

Egenskaper

- I fargen ren hvit, blank: består av 85 % resirkulert plast.

Tekniske data

| | |
|--|--------------------------|
| Dekkramme enk.: | B 90,0 x H 90,0 x T 3,4 |
| Dekkramme dob.: | B 90,0 x H 161,1 x T 3,4 |
| Dekkramme 3-d: | B 90,0 x H 232,6 x T 3,4 |
| Dekkramme 4-d: | B 90,0 x H 303,9 x T 3,4 |
| Hjørneradius: | R 0,3 |
| Biocirkulær plast - Farge: renhvit glans: | min. 50 % |