







Dekkramme Gira F100 renhvit silkematt (lakkert)



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 172	1/10		4010337133506
 Dobbel	0212 172	1/10		4010337133513
 dobbel, uten mellomstykke	1002 172	1/10		4010337133551
 3-dobbel	0213 172	1/5		4010337133520
 4-dobbel	0214 172	1/5		4010337133537
 5-dobbel	0215 172	1/5		4010337133544

Egenskaper

- I fargen ren hvit, blank: består av 85 % resirkulert plast.

Tekniske data

Dekkramme enk.:	B 83,3 x H 83,3 x T 10,6
Dekkramme dob.:	B 83,3 x H 154,4 x T 10,6
Dekkramme dob. u/MS:	B 83,3 x H 154,4 x T 10,6

Dekkramme 3-d:	B 83,3 x H 225,9 x T 10,6
Dekkramme 4-d:	B 83,3 x H 297,2 x T 10,6
Dekkramme 5-d:	B 83,3 x H 368,5 x T 10,6
Hjørneradius:	R 3
Biocirkulær plast - Farge: renhvit glans:	min. 50 %
