







Dekkramme Gira F100 antrasitt (lakkert)



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|---|-----------------|------|----|---------------|
|  Enkel | 0211 173 | 1/10 | | 4010337135951 |
|  Dobbel | 0212 173 | 1/10 | | 4010337133568 |
|  dobbel, uten mellomstykke | 1002 173 | 1/10 | | 4010337133605 |
|  3-dobbel | 0213 173 | 1/5 | | 4010337133575 |
|  4-dobbel | 0214 173 | 1/5 | | 4010337133582 |
|  5-dobbel | 0215 173 | 1/5 | | 4010337133599 |

Egenskaper

- I fargen ren hvit, blank: består av 85 % resirkulert plast.

Tekniske data

| | |
|----------------------|---------------------------|
| Dekkramme enk.: | B 83,3 x H 83,3 x T 10,6 |
| Dekkramme dob.: | B 83,3 x H 154,4 x T 10,6 |
| Dekkramme dob. u/MS: | B 83,3 x H 154,4 x T 10,6 |

| | |
|--|---------------------------|
| Dekkramme 3-d: | B 83,3 x H 225,9 x T 10,6 |
| Dekkramme 4-d: | B 83,3 x H 297,2 x T 10,6 |
| Dekkramme 5-d: | B 83,3 x H 368,5 x T 10,6 |
| Hjørneradius: | R 3 |
| Biocirkulær plast - Farge: renhvit glans: | min. 50 % |
