








Dekkramme Gira E2 grå matt



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 37	1/10		4010337077299
 1,5-dobbel	1001 37	1/10		4010337082422
 Dobbel	0212 37	1/10		4010337077589
 dobbel, uten mellomstykke	1002 37	1/10		4010337082439
 3-dobbel	0213 37	1/5		4010337077602
 4-dobbel	0214 37	1/5		4010337077626
 5-dobbel	0215 37	1/5		4010337077640

Egenskaper

- Plast: halogenfri, slag- og bruddsikker termoplast, eller heter det da polykarbonat.

Merknader

- Også egnet for kanalinstallasjoner.
 - Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.
-