







Dekkramme Gira F200 grå matt (lakkert)



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 76	1/10		4010337113164
 Dobbel	0212 76	1/10		4010337113218
 dobbel, uten mellomstykke	1002 76	1/10		4010337113423
 3-dobbel	0213 76	1/5		4010337113263
 4-dobbel	0214 76	1/5		4010337113324
 5-dobbel	0215 76	1/5		4010337113379

Egenskaper

- I fargen ren hvit, blank: består av 85 % resirkulert plast.

Tekniske data

Dekkramme enk.:	B 90,0 x H 90,0 x T 11,4
Dekkramme dob.:	B 90,0 x H 161,1 x T 11,4
Dekkramme dob. u/MS:	B 90,0 x H 161,1 x T 11,4

Dekkramme 3-d:	B 90,0 x H 232,6 x T 11,4
Dekkramme 4-d:	B 90,0 x H 303,9 x T 11,4
Dekkramme 5-d:	B 90,0 x H 375,2 x T 11,4
Hjørneradius:	R 0,3
Biocirkulær plast - Farge: renhvit glans:	min. 50 %
