







## Dekkramme Gira F300 grå matt (lakkert)



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 86	1/10		4010337113492
 Dobbel	0212 86	1/10		4010337113522
 dobbel, uten mellomstykke	1002 86	1/10		4010337131915
 3-dobbel	0213 86	1/5		4010337113577
 4-dobbel	0214 86	1/5		4010337113621
 5-dobbel	0215 86	1/5		4010337131908

### Egenskaper

- I fargen ren hvit, blank: består av 85 % resirkulert plast.

### Tekniske data

Dekkramme enk.:	B 80,8 x H 80,8 x T 11,4
Dekkramme dob.:	B 80,8 x H 151,9 x T 11,4
Dekkramme dob. u/MS:	B 80,8 x H 151,9 x T 11,4

Dekkramme 3-d:	B 80,8 x H 223,4 x T 11,4
Dekkramme 4-d:	B 80,8 x H 297,7 x T 11,4
Dekkramme 5-d:	B 80,8 x H 366,0 x T 11,4
Hjørneradius:	R 0,5
Biocirkulær plast - Farge: renhvit glans:	min. 50 %

---