








Dekkramme Gira Standard 55 renhvit glans



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|---|--------------------|----------|----|---------------|
|  Enkel | 0211 03 1420752 | 1/10/100 | | 4010337211037 |
|  1,5-dobbel | 1001 03 1522581 | 1/10 | | 4010337881308 |
|  Dobbel | 0212 03 1420753 | 1/10/100 | | 4010337212034 |
|  dobbel, uten mellomstykke | 1002 03 1420751 | 1/10 | | 4010337001607 |
|  3-dobbel | 0213 03 1420754 | 1/10/100 | | 4010337213031 |
|  4-dobbel | 0214 03 1420755 | 1/5 | | 4010337214038 |
|  5-dobbel | 0215 03 1420756 | 1/5 | | 4010337215035 |

Egenskaper

- Plast: halogenfri, slag- og bruddsikker termoplast, eller heter det da polykarbonat.

Merknader

- Også egnet for kanalinstallasjoner.
 - Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.
-