

## Dekkramme Gira E2 renhvit silkematt



| Spesifikasjon                                                                                                 | Bestillings nr.    | PE       | PS | EAN           |
|---------------------------------------------------------------------------------------------------------------|--------------------|----------|----|---------------|
|  Enkel                       | 0211 22<br>1420510 | 1/10/100 |    | 4010337211228 |
|  1,5-dobbel                | 1001 22<br>1522590 | 1/10     |    | 4010337881322 |
|  Dobbel                    | 0212 22<br>1420512 | 1/10/100 |    | 4010337212225 |
|  dobbel, uten mellomstykke | 1002 22<br>1420204 | 1/10     |    | 4010337002222 |
|  3-dobbel                  | 0213 22<br>1420514 | 1/5      |    | 4010337213222 |
|  4-dobbel                  | 0214 22<br>1420516 | 1/5      |    | 4010337214229 |
|  5-dobbel                  | 0215 22<br>1420518 | 1/5      |    | 4010337215226 |

## Egenskaper

- Plast: halogenfri, slag- og bruddsikker termoplast, eller heter det da polykarbonat.

## Merknader

- Også egnet for kanalinstallasjoner.
  - Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.
-