

## Dekkramme Gira E2 grå matt



| Spesifikasjon                                                                                                 | Bestillings nr. | PE   | PS | EAN           |
|---------------------------------------------------------------------------------------------------------------|-----------------|------|----|---------------|
|  Enkel                       | 0211 37         | 1/10 |    | 4010337077299 |
|  1,5-dobbel                | 1001 37         | 1/10 |    | 4010337082422 |
|  Dobbel                    | 0212 37         | 1/10 |    | 4010337077589 |
|  dobbel, uten mellomstykke | 1002 37         | 1/10 |    | 4010337082439 |
|  3-dobbel                  | 0213 37         | 1/5  |    | 4010337077602 |
|  4-dobbel                  | 0214 37         | 1/5  |    | 4010337077626 |
|  5-dobbel                  | 0215 37         | 1/5  |    | 4010337077640 |

## Egenskaper

- Plast: halogenfri, slag- og bruddsikker termoplast, eller heter det da polykarbonat.

## Merknader

- Også egnet for kanalinstallasjoner.
  - Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.
-