








Dekkramme Gira Standard 55 kremhvit glans



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 01 1420705	1/10/100		4010337211013
 1,5-dobbel	1001 01	1/10		4010337881247
 Dobbel	0212 01 1420706	1/10/100		4010337212010
 dobbel, uten mellomstykke	1002 01	1/10		4010337002017
 3-dobbel	0213 01 1420707	1/10/100		4010337213017
 4-dobbel	0214 01 1420708	1/5		4010337214014
 5-dobbel	0215 01 1420709	1/5		4010337215011

Egenskaper

- Plast: halogenfri, slag- og bruddsikker termoplast, eller heter det da polykarbonat.

Merknader

- Også egnet for kanalinstallasjoner.
 - Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.
-