







Dekkramme Gira F100 renhvit glans



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 112 1401698	-	-	4010337043973
 Dobbel	0212 112 1401699	-	-	4010337044017
 dobbel, uten mellomstykke	1002 112	-	-	4010337047094
 3-dobbel	0213 112 1404400	-	-	4010337044031
 4-dobbel	0214 112 1404401	-	-	4010337044055
 5-dobbel	0215 112 1404402	-	-	4010337044079

Egenskaper

- Bruddsikker.
- I fargen ren hvit, blank: består av 85 % resirkulert plast.

Tekniske data

Dekkramme enk.:	B 83,3 x H 83,3 x T 10,6
Dekkramme dob.:	B 83,3 x H 154,4 x T 10,6
Dekkramme dob. u/MS:	B 83,3 x H 154,4 x T 10,6

Dekkramme 3-d:	B 83,3 x H 225,9 x T 10,6
Dekkramme 4-d:	B 83,3 x H 297,2 x T 10,6
Dekkramme 5-d:	B 83,3 x H 368,5 x T 10,6
Hjørneradius:	R 3
Biocirkulær plast - Farge: renhvit glans:	min. 50 %
