







Dekkramme Gira F300 renhvit glans



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|---|-----------------|------|----|---------------|
|  Enkel | 0211 80 | 1/10 | | 4010337113478 |
|  Dobbel | 0212 80 | 1/10 | | 4010337113539 |
|  dobbel, uten mellomstykke | 1002 80 | 1/10 | | 4010337131830 |
|  3-dobbel | 0213 80 | 1/5 | | 4010337113584 |
|  4-dobbel | 0214 80 | 1/5 | | 4010337113638 |
|  5-dobbel | 0215 80 | 1/5 | | 4010337131823 |

Egenskaper

- I fargen ren hvit, blank: består av 85 % resirkulert plast.

Tekniske data

| | |
|----------------------|---------------------------|
| Dekkramme enk.: | B 80,8 x H 80,8 x T 11,4 |
| Dekkramme dob.: | B 80,8 x H 151,9 x T 11,4 |
| Dekkramme dob. u/MS: | B 80,8 x H 151,9 x T 11,4 |

| | |
|--|---------------------------|
| Dekkramme 3-d: | B 80,8 x H 223,4 x T 11,4 |
| Dekkramme 4-d: | B 80,8 x H 297,7 x T 11,4 |
| Dekkramme 5-d: | B 80,8 x H 366,0 x T 11,4 |
| Hjørneradius: | R 0,5 |
| Biocirkulær plast - Farge: renhvit glans: | min. 50 % |
