


Dekkramme Gira Standard 55 med tekstfelt kremhvitt glans



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	1091 01	1/10		4010337091011
 Dobbel vannrett	1092 01	1/10		4010337092018
 Dobbel lodrett	1102 01	1/10		4010337102014
 3-dobbel vannrett	1093 01	1/5		4010337093015
 3-dobbel vertikal	1103 01	1/5		4010337103011
 4-dobbel vannrett	1094 01	1/5		4010337094012
 4-dobbel loddrett	1114 01	1/5		4010337008903
 5-dobbel vannrett	1095 01	1/5		4010337095019
 5-dobbel loddrett	1115 01	1/5		4010337115014

Egenskaper

- Plast: halogenfri, slag- og bruddsikker termoplast, eller heter det da polykarbonat.
 - Sprøytetåketett.
 - Dekkramme med transparent vindu for merking av innsatsene.
 - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
-

Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggghus av flat konstruksjon, påveggghus.
-